

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

0.22" Travel, X Axis, Extended Travel, Micro Series (A)



Stock #56-419 [CONTACT US](#)



1



€283,00

ADD TO CART

Qty 1+

€283,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Fine Screw (80 Pitch)

Drive Orientation:
Center Drive

Type: English
Stage Size (mm): 11.2 x 26.2
Travel (mm): 5.6
Travel (inches): 0.22
Center Hole: 0.155" (3.9mm) Thru with 8-32 TPI Threaded
Construction: Aluminum Body, Stainless Steel Rails
Load Capacity, Normal (kg): 0.25
Note: Without Covered Rails
Stage Size (inches): 0.44 x 1.03
Straight Line Accuracy (µm): 1.5
Weight (g): 2.5
Wobble (mrad): 0.01

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View