

TECHSPEC® 0.25X MercuryTL™ Liquid Lens Telecentric Lens



0.24X MercuryTL™ Liquid Lens Telecentric Lens, #36-189



Stock **#36-189** 3-4 DAYS

- 1 +

€2.130,00

ADD TO CART

Qty 1+

€2.130,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
155.50

Horizontal Field of View, 1/2" Sensor:
26.5mm

Filter Thread:
M46 x0.75 (Female)

Weight (g):

266
Horizontal Field of View, 1/3" Sensor: 19.9mm
Stock No. of Mounting Clamp: #56-870 Sold Separately
Note: MercuryTL™
Horizontal Field of View, 1/1.8" Sensor: 28.8mm
Typical Telecentricity @ 588nm (°): <0.051
Typical Distortion @ 588nm (%): <0.4
Mounting Diameter (mm): 48
Type: Telecentric Lens
Primary Magnification PMAG: 0.25X
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 91 - 173
Mount: C-Mount
Aperture (f/#): f/10
FOV @ Max Sensor Format, H x V (mm): 28.8 x 21.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View