

TECHSPEC® 0.3 OD 12.5mm Diameter, Reflective ND Filter



Stock **#46-131** 3-4 DAYS

- 1 + **€34,00**

ADD TO CART

Qty 1-5
€34,00
Qty 6+
€27,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0

Optical Density OD (Average):
0.3

Substrate: Float Glass
Coating: Surface 1: Inconel
Reflection (%): 21.00
Surface Quality: 80-50
Thickness (mm): 1.60 Nominal
Transmission (%): 50.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): 80
Neutrality: ±5% of Optical Density
Note: Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant