

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 0.3 OD 25mm Dia UV-NIR ND Filter



UV-NIR Neutral Density Filters

Stock #88-270 3-4 DAYS



1



€167,00

ADD TO CART

Qty 1-5

€167,00

Qty 6+

€149,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Optical Density OD (Average):
0.3

Substrate: ☐

Fused Silica (Coming 7980)	
Coating:	Metallic Based ND
Surface Quality:	40-20
Thickness (mm):	3.00 ±0.10
Transmission (%):	50.0
Type:	Neutral Density Filter
Blocking Wavelength Range (nm):	190 - 1700
Clear Aperture (%):	80.00
Transmitted Wavefront, P-V:	λ/4
Optical Density Tolerance (%):	±10
Parallelism (arcsec):	<5

Regulatory Compliance

RoHS 2015:	Compliant
Reach 219:	Compliant
Certificate of Conformance:	View