

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

## 0.3 OD M58.0 X 0.75, Mounted Absorptive ND Filter



Stock #54-731 CLEARANCE CONTACT US



1



€38,95

ADD TO CART

Qty 1+

€38,95

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):  
0.3

Clear Aperture CA (mm):  
54.0

Filter Thread:  
M58 x0.75

Substrate:   
ND Filter Glass

Thickness with Mount (mm):  
5.00

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Surface Quality:</b><br>80-50                                      |
| <b>Transmission (%):</b><br>50                                        |
| <b>Type:</b><br>Mounted Imaging Filter                                |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700                   |
| <b>Mount Thickness (mm):</b><br>3.8 ±0.1                              |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                          |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @400 - 700nm |
| <b>Mount Diameter (mm):</b><br>60.0 +0/-0.2                           |
| <b>Mount Thickness Including Threads (mm):</b><br>6.3                 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |