

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



UV-NIR Neutral Density Filters

Stock #19-297 3-4 DAYS



1



€266,00

ADD TO CART

Qty 1-5

€266,00

Qty 6+

€238,70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.2

Optical Density OD (Average):
0.4

Substrate:

Fused Silica (Coming 7980)	
Coating:	Metallic Based ND
Surface Quality:	40-20
Thickness (mm):	5.00 ±0.10
Transmission (%):	40.0
Type:	Neutral Density Filter
Blocking Wavelength Range (nm):	190 - 1700
Clear Aperture (%):	80.00
Transmitted Wavefront, P-V:	λ/4
Optical Density Tolerance (%):	±10
Parallelism (arcsec):	<5

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View