

TECHSPEC® 0.5 OD 25mm Diameter UV-VIS ND Filter



Stock **#47-206** 3-4 DAYS

- 1 + **€115,00**

ADD TO CART

Qty 1-5
€115,00

Qty 6+
€92,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 25.00 +0.00/-0.20
Optical Density OD (Average): 0.5
Substrate: ☐ Fused Silica (Corning 7980)

Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.10
Transmission (%): 32.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 250 - 700
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant