

TECHSPEC® 0.5X - 1.0X VariMagTL™ Telecentric Lens



0.5X- 1.0X VariMagTL™ Telecentric Lens, #88-386

Stock **#88-386** ☐ In Stock

- 1 + **€1.630,00**

ADD TO CART

Qty 1+

€1.630,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
175.48

Filter Thread:
M40.5 x0.50 (Female)

Maximum Diameter (mm):
50.8

Resolution:
75 lp/mm @ >20%

Weight (g):

642
Typical Telecentricity @ 588nm (°): <0.1
Typical Distortion @ 588nm (%): <0.1
Type: Telecentric Lens
Primary Magnification PMAG: 0.5X- 1.0X
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - 115
Mount: C-Mount
Style: Telecentric, Variable Magnification
Aperture (f/#): f/6 - Closed
FOV @ Max Sensor Format, H x V (mm): 17.6 x 13.2 - 8.8 x 6.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View