

0.65X - 4.6X Dynamic Focus VZM™ Lens



Dynamic Focus VZM™ Lens

Stock **#89-999** CLEARANCE 3-4 DAYS

-

1

+

€1.456,95

ADD TO CART

Qty 1+
€1.456,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm): 248.00
Filter Thread: M22.5 x 0.50
Working Distance Tolerance (mm): ±3
Zoom Ratio: 7:1
Type:

Zoom Lens
Primary Magnification PMAG: 0.65X - 4.6X
Maximum Sensor Format: 2/3"
Working Distance (mm): 87.00
Style: Liquid Lens
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View