

0.7 OD, 25mm Dia., IR Neutral Density Filter



Infrared (IR) Neutral Density (ND) Filters

Stock #12-000 3-4 DAYS



1



€384,00

ADD TO CART

Qty 1-10

€384,00

Qty 11+

€344,90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 ±0.2

Optical Density OD (Average):
0.7

Substrate: ☐
Germanium (Ge)

Coating: Metallic Based ND
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 20.0
Transmission Tolerance (%): ±2.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 2000 - 14,000
Parallelism (arcmin): <10
Clear Aperture (%): 90
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant