

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



0.75X MercuryTL™ Liquid Lens Telecentric Lens, #36-192



Stock #36-192 3-4 DAYS



1



€2.130,00

ADD TO CART

Qty 1+

€2.130,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
148.70

Horizontal Field of View, 1/2" Sensor:
8.7mm

Horizontal Field of View, 2/3" Sensor:
11.7mm

Filter Thread:

M30.5 x 0.50 (Female)
Weight (g): 222
Horizontal Field of View, 1/3" Sensor: 6.5mm
Stock No. of Mounting Clamp: #56-870 Sold Separately
Note: MercuryTL™
Typical Telecentricity @ 588nm (°): <0.057
Typical Distortion @ 588nm (%): <0.04
Mounting Diameter (mm): 36
Type: Telecentric Lens
Primary Magnification PMAG: 0.75X
Maximum Sensor Format: 2/3"
Working Distance (mm): 85 - 99
Mount: C-Mount
Aperture (f/#): f/10
FOV @ Max Sensor Format, H x V (mm): 11.7 x 8.8
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View