

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

0.9 OD M39.0 X 0.50, Mounted Absorptive ND Filter



Stock #59-176 3-4 DAYS



1



€43,00

ADD TO CART

Qty 1-9

€43,00

Qty 10+

€40,60

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
34.0

Filter Thread:
M39 x0.50

Substrate: 

ND Filter Glass
Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 12.5
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 41.0 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View