

Siemens Star Target, 4" x 4", 120 Sectors Photo Paper



Photo Paper Star Target

Stock **#46-246** 3-4 DAYS



1



€125,00

ADD TO CART

Qty 1-4

€125,00

Qty 5+

€118,90

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Frequency (lp/mm):
0.6112 - 15.28

Substrate:
Photo Paper

Line Width (mm):
0.033 - 0.818

Number of Sectors: 120.00
Optical Density OD (Average): >1.6
Pattern Diameter (mm): 62.5
Dimensions (inches): 4 x 4 ±0.004
Thickness (mm): 0.20 ±nominal
Wedge Angle: 3°
Unresolved Core Diameter (mm): 2.5
Note: Emulsion Coated
NIST Certification: No

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant