

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

10 X 10mm 120 Grit Ground Glass Diffuser



Stock #83-083 3-4 DAYS

1 €17,75

ADD TO CART

Qty 1-10
€17,75

Qty 11+
€15,25

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating: Uncoated
Dimensional Tolerance (mm): ±0.25
Dimensions (mm): 10.00 x 10.00
Edges:

Cut Edges
Grit: ☐ 120
Substrate: ☐ Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 10.00
Note: Sandblasted on first surface
Length (mm): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant