

254.0mm/10.0" Optic Dia., Optical Cell Kinematic Mount



Stock #36-478 3-4 DAYS

- 1 + **€4.883,00**

ADD TO CART

Qty 1-4
€4.883,00
Qty 5+
€4.549,40
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads
Type: Adjustable - Tip-Tilt
Type of Optics: Circular
Size of Compatible Optics (mm):

254.0
Clear Aperture CA (inches): 9.58
Clear Aperture CA (mm): 243.3
Optical Centerline (mm): 203.2
Range: 7°
Dimensions (inches): 16.00 x 8.00 x 15.00
Dimensions (mm): 406.4 x 203.2 x 381.0
Weight (lbs): 52.0
Inner Diameter (inches): 10.06
Construction: Black Anodized Aluminum, Stainless Steel
Diameter of Compatible Optics (inches): 10.00
Optical Centerline (inches): 8.00
Optic Holding Style: Three Spring-Loaded Clips
Max. Thickness of Compatible Optics (mm): 43.5
Adjustment Screw Pitch (inches): 0.031

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View