

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-252 3-4 DAYS

[Additional Bandwidths](#)



1



€597,00

ADD TO CART

Qty 1-9

€597,00

Qty 10+

€537,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

25.00 +0.00/-0.20

Angle of Incidence (°):

0

Optical Density OD (Average):

≥3.0

Clear Aperture CA (mm): 20.0
Center Wavelength CWL (nm): 10,000.00 ±100
Full Width-Half Max FWHM (nm): 500.00 ±50
Substrate:  Silicon Floatzone (SiFz)
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): ≥65 (at peak)
Type: Bandpass Filter
Typical Applications: Ammonia (NH ₃) Detection
Blocking Wavelength Range (nm): 200 - 16000
Center Wavelength CWL (μm): 10.00 ±0.100
Full Width-Half Max FWHM (μm): 0.50 ±0.05

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View