

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock #13-511 3-4 DAYS



1



€1.075,00

ADD TO CART

Qty 1-5

€1.075,00

Qty 6+

€860,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
100.00 +0.00/-0.10

Effective Focal Length EFL (mm):
200.00 @ 780nm

Numerical Aperture NA:
0.25

Back Focal Length BFL (mm): 187.43
Substrate: ☐ N-BK7
Aspheric Design Wavelength (nm): 780
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 92
Edge Thickness ET (mm): 6.45
Center Thickness CT (mm): 19.00 ±0.10
f#: 2.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Power (diopters): 5.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View