

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

100mm Dia X 12.5mm FL Alum. Coated, Parabolic Reflector



Stock #90-964 [CONTACT US](#)



1



€356,00

ADD TO CART

Qty 1-10

€356,00

Qty 11+

€313,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: [BOROFLOAT®](#)

Diameter (mm):
100.00 +0.0/-0.5

Focal Length FL (mm):
12.50

Aperture (f#):

0.125
Coating: Protected Aluminum (400-700nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating Type: Metal
Center Hole Diameter (mm): No Center Hole
Height (mm): 48.2 ±0.5
Type: Parabolic Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View