

# 100mW, 1064nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock #19-474 3-4 DAYS

⊖ 1 ⊕ **€680,00**

**ADD TO CART**

Qty 1-9

€680,00

Qty 10+

€612,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Operating Temperature (°C):**  
23 to 27

**Operating Voltage (V):**  
3

**Output Power (mW):**  
100

**Spatial Mode:**  
TEM<sub>00</sub>

**Wavelength (nm):**  
1,064.00 ±2

**Wavelength Tolerance (nm):**  
±2

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#19-475](#)  
Europe: [#19-475](#)  
Japan: Not Available  
Korea: Not Available  
China: [#19-475](#)

**Modulation Frequency (kHz):**  
Not Modulated

**Note:**  
Compatible TEC Controller ([#19-476](#)) sold separately

**Beam Diameter (mm):**  
1.5 Typical

**Beam Divergence (mrad):**  
<1.5 Typical

**Laser Class - CDRH:**  
IIIb

**Color:**  
Infrared

**Length (mm):**  
90.00

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 233:**  
[Compliant](#)