

**TECHSPEC® 101.6 x 326.7mm EFL 30° Protected Aluminum 100Å Off-Axis Parabolic Mirror**



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#35-584** 3-4 DAYS

[Other Coating Options](#)



1



€925,00

ADD TO CART

Qty 1-5

€925,00

Qty 6+

€832,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:  
Off-Axis Parabolic Mirror

Diameter (mm):  
101.60 +0.00/-0.38

Effective Focal Length EFL (mm):

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| 326.69                                                                                                           |
| <b>Focal Length Tolerance (%):</b><br>±1                                                                         |
| <b>Radius of Curvature (mm):</b><br>609.60                                                                       |
| <b>Coating:</b><br>Protected Aluminum (400-2000nm)                                                               |
| <b>Coating Type:</b><br>Metal                                                                                    |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≥85% @ 400 - 700nm<br>R <sub>avg</sub> ≥97% @ 2,000 - 12,000nm |
| <b>Off-Set Angle (°):</b><br>30                                                                                  |
| <b>Parent Focal Length PFL (mm):</b><br>304.8                                                                    |
| <b>Surface Figure, RMS:</b><br>1λ                                                                                |
| <b>Surface Roughness (Angstroms):</b><br><100 RMS                                                                |
| <b>Wavelength Range (nm):</b><br>400 - 2000                                                                      |
| <b>Clear Aperture (%):</b><br>90                                                                                 |
| <b>Surface Quality:</b><br>80-50                                                                                 |
| <b>Compatible Mounting Plates:</b><br><a href="#">#83-977</a>                                                    |
| <b>Substrate:</b><br>Aluminum 6061-T6                                                                            |
| <b>Y Offset (mm):</b><br>163.34                                                                                  |
| <b>Reflected Wavefront, RMS:</b><br>2λ                                                                           |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |