

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

10.5mm Diameter x 9.45mm FL, Aspneric Condenser Lens



Stock #43-985 ☐ In Stock

[Other Coating Options](#)



1



€43,00

ADD TO CART

Qty 1-10

€43,00

Qty 11+

€38,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
10.50 +0.00/-0.15

Effective Focal Length EFL (mm):
9.45

Numerical Aperture NA:
0.56

Back Focal Length BFL (mm): 8.10
Substrate: N-F2
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 9.8
Edge Thickness ET (mm): 1.1
Center Thickness CT (mm): 3.80 ±0.2
f/#: 0.9
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 10.5
Radius R ₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 350 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View