

10mW, 589nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock **#19-472** [CONTACT US](#)

- 1 + **€1.575,00**

ADD TO CART

Qty 1-9
€1.575,00
Qty 10+
€1.418,00
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
23 to 27

Operating Voltage (V):
3

Output Power (mW):
10

Spatial Mode: TEM ₀₀
Wavelength (nm): 589.00 ±2
Wavelength Tolerance (nm): ±2
Power Supply: Power Supply Required and Sold Separately: USA: #19-475 Europe: #19-475 Japan: Not Available Korea: Not Available China: #19-475
Modulation Frequency (kHz): Not Modulated
Note: Compatible TEC Controller (#19-476) sold separately
Beam Diameter (mm): 1.5 Typical
Beam Divergence (mrad): <1.5 Typical
Laser Class - CDRH: IIIb
Color: Yellow
Length (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant