

## 22.2mm Aperture, 51mm FL UV/VIS Fiber Refocusing Assembly



Fiber Refocusing Assembly

Stock #17-574 3-4 DAYS



1



€615,00

ADD TO CART

Qty 1-10

€615,00

Qty 11+

€544,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
28.58

Substrate: ☐  
[Fused Silica](#) (Corning 7980)

Type:  
Refocusing Assembly

|                                                                                                     |
|-----------------------------------------------------------------------------------------------------|
| <b>Wavelength Range (nm):</b><br>190 - 1250                                                         |
| <b>Aperture Size:</b><br>22.2                                                                       |
| <b>Focal Length FL (mm):</b><br>51.00                                                               |
| <b>Housing Material:</b><br>Anodized Aluminum                                                       |
| <b>Length (mm):</b><br>25.40                                                                        |
| <b>Note:</b><br>Compatible with <a href="#">#17-567</a> & <a href="#">#17-569</a> Fiber Collimators |
| <b>Operating Temperature (°C):</b><br>-40 to 100                                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |