

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Precision Ultraviolet Mirrors

Stock #18-740 3-4 DAYS



1



€273,00

ADD TO CART

Qty 1-5

€273,00

Qty 6+

€218,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.2

Surface Flatness (P-V):
λ/10

Substrate: ☐

Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} ≥92% @ 190 - 250nm R _{avg} ≥83% @ 250 - 900nm
Coating: Enhanced Aluminum (190-900nm)
Coating Type: Metal
Angle of Incidence (°): 0
Clear Aperture (%): 90
Design Wavelength DWL (nm): 190
Parallelism (arcsec): <30
Thickness (mm): 2.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 190 - 900
Vacuum Compatibility: 10 ⁻⁷ Torr

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View