

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union




SUBMIT

TECHSPEC® 10mm Aperture X 175mm L Low NA, Fused Silica Light Pipe



Fused Silica Light Pipe Homogenizing Rods



Stock #65-839 3-4 DAYS



1



€347,50

ADD TO CART

Qty 1-5

€347,50

Qty 6+

€278,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate:

Fused Silica (Corning 7980)
Length (mm): 175.00
Surface Quality: 60-40
Type: Light Pipe
Entrance and Exit Aperture (mm): 10.00
Parallelism (arcmin): 5.00
Length Tolerance (mm): ±0.3
Aperture Tolerance (mm): ±0.10
Image Orientation: Light Homogenization
Light Source NA: Low
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): 3λ
#Sorting: 61.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
