

10mm Dia. x 10mm EFL Arton Plastic Asphere



Stock #90-206 3-4 DAYS

- 1 + **€45,00**

ADD TO CART

Qty 1-10
€45,00
Qty 11+
€37,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
10.00

Effective Focal Length EFL (mm):
10.00 ±0.2

Numerical Aperture NA:
0.40

Back Focal Length BFL (mm):

8.28
Substrate: □ Arton Plastic
Coating: Uncoated
Clear Aperture CA (mm): 8.00
Edge Thickness ET (mm): 3.1
f/#: 1.25
Bevel: Protective bevel as needed
Flange Distance (mm): 8.28
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View