

TECHSPEC® 10mm Diameter 45° Rod Mirror Aluminum Coated



45° Rod Mirrors

Stock **#45-944** ☒ In Stock

-

1

+

€137,00

ADD TO CART

Qty 1-5

€137,00

Qty 6+

€123,30

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
15.00

Coating:
Protected Aluminum (400-700nm)

Angle Tolerance (arcmin):
±10

Bevel: Protective bevel as needed
Coating Specification: R _{avg} >85% @400 - 700nm
Coating Type: Metal
Diameter (mm): 10.00 +0.00/-0.05
Length Tolerance (mm): ±0.1
Ray Deviation (°): 90.00
Substrate: ☐ N-BK7
Surface Quality: 40-20
Type: Rod Lens
Wavelength Range (nm): 400 - 700
Note: Coating on Elliptical Surface
Damage Threshold, By Design: ☐ 0.3 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
