

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 10mm Diameter MgF₂ Coated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock **#32-947** □ In Stock

-

1

+

€34,50

ADD TO CART

Qty 1-5

€34,50

Qty 6+

€27,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
58.3

Bevel:
Protective as needed

Clear Aperture CA (mm):
9.00

Diameter (mm): 10.00 ±0.25
Thickness (mm): 1.00
Coating: MgF₂ (632.8nm)
Coating Specification: R_{avg} ≤1.50% @ 632.8nm (N-BK7)
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 9.4 (+20 to +300°C)
Density (g/cm³): 2.56
Edges: Fine Ground
Index of Refraction n_d: 1.523
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.22
Substrate: B270
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 400 - 700
Young's Modulus (GPa): 71.5
Damage Threshold, By Design: ☐ 10 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant