

10mW, 589nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock #19-472 3-4 DAYS

⊖ 1 ⊕ **€1.575,00**

ADD TO CART

Qty 1-9

€1.575,00

Qty 10+

€1.418,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
23 to 27

Operating Voltage (V):
3

Output Power (mW):
10

Spatial Mode:
TEM₀₀

Wavelength (nm):
589.00 ±2

Wavelength Tolerance (nm):
±2

Power Supply:
Power Supply Required and Sold Separately.
USA: [#19-475](#)
Europe: [#19-475](#)
Japan: Not Available
Korea: Not Available
China: [#19-475](#)

Modulation Frequency (kHz):
Not Modulated

Note:
Compatible TEC Controller ([#19-476](#)) sold separately

Beam Diameter (mm):
1.5 Typical

Beam Divergence (mrad):
<1.5 Typical

Laser Class - CDRH:
IIIb

Color:
Yellow

Length (mm):
100.00

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)