

16mm Focal Length Lens, 1.1" Sensor Format



Compact Fixed Focal Length Lenses for 1.1" Sensors

Stock **#14-112** 3-4 DAYS

[Similar Products](#)

- 1 + **€1.040,00**

ADD TO CART

Qty 1+

€1.040,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
35.20

Filter Thread:
M34 x0.50

Maximum Diameter (mm):
39.5

Weight (g): 91.4
Maximum Image Circle (mm): 17.60
Horizontal Field of View @ Max Sensor Format: 48.2°
Horizontal Field of View, 1.1" Sensor: 48.2°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 16.00
Maximum Sensor Format: 1.1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8 - f/16
Distortion (%): -0.5
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View