

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25mm Focal Length Lens, 1.1" Sensor Format



Compact Fixed Focal Length Lenses for 1.1" Sensors

Stock #14-113 3-4 DAYS

[Similar Products](#)



1



€1.040,00

ADD TO CART

Qty 1+

€1.040,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
34.00

Filter Thread:
M34 x0.50

Maximum Diameter (mm):
39.5

Weight (g): 78.6
Maximum Image Circle (mm): 17.60
Horizontal Field of View @ Max Sensor Format: 31.7°
Horizontal Field of View, 1.1" Sensor: 31.7°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Maximum Sensor Format: 1.1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8 - f/16
Distortion (%): 0.3
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View