

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

11" X 11" , 0.085" FL, Lenticular Array



Stock #43-028 ☐ In Stock



1



€128,00

ADD TO CART

Qty 1-10

€128,00

Qty 11+

€112,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):

2.16

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Lens Array
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.085
Center Thickness CT (mm): 2.20
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 11 x 11
Dimensions (mm): 279.4 x 279.4
Effective Focal Length EFL (inches): 0.085
Effective Size (inches): 11 x 11
Index of Refraction n_d: 1.49
Number of Lenses: 64 per 25.4mm
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Thickness Tolerance (mm): ±0.88

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View