

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

# Richardson Gratings™ 1200 Grooves, 12.7 X 12.7mm, 250nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #15-760 3-4 DAYS

1

€131,00

ADD TO CART

Qty 1+

€131,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):  
1200

Wavelength Range (nm):

|                                                           |
|-----------------------------------------------------------|
| 175 - 400                                                 |
| <b>Blaze Wavelength (nm):</b><br>250 ±25                  |
| <b>Blaze Angle (°):</b><br>8.6                            |
| <b>Peak Efficiency, Typical (%):</b><br>62                |
| <b>Dimensions (mm):</b><br>12.7 x 12.7 ±0.1               |
| <b>Clear Aperture (%):</b><br>>90                         |
| <b>Coating:</b><br>Aluminium                              |
| <b>Construction:</b><br>Ruled Grating                     |
| <b>Length (mm):</b><br>12.70                              |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass |
| <b>Thickness (mm):</b><br>6.00 ±0.5                       |
| <b>Type:</b><br>Reflective Diffraction Grating            |
| <b>Width (mm):</b><br>12.70                               |
| <b>Reflected Wavefront, RMS:</b><br>λ/4                   |
| <b>Centering of Ruled Area on Substrate (mm):</b><br>±1   |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.15         |
| <b>Groove Spacing Tolerance (%):</b><br><0.05             |
| <b>Polarization:</b><br>S, P and Average                  |
| <b>Master Reference:</b><br>2840                          |
| <b>Spectral Order (m):</b><br>1                           |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br>Compliant                                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |