

1200 Grooves, 50mm Sq, 36.9° Groove Angle Grating



Stock #49-586 3-4 DAYS

⊖ 1 ⊕

€225,00

ADD TO CART

Qty 1-9
€225,00

Qty 10+
€202,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
400 - 700

Blaze Angle (°):
36.9

Dimensions (mm): 50.00 x 50.00
Construction: Blazed (Ruled) Grating
Length (mm): 50.00
Substrate: ☐ B270
Thickness (mm): 3.00 ±0.5
Type: Transmission Diffraction Grating
Wavelength: VIS
Width (mm): 50.00
Alignment of Grooves to Edge (°): ±0.5
Groove Angle (°): 36.9

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View