

TECHSPEC® 12.5mm 1064nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-869** 3-4 DAYS



1



€253,00

ADD TO CART

Qty 1-5

€253,00

Qty 6+

€198,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification: R_{abs} <0.25% @ 1064nm
Construction: Cube
Design Wavelength DWL (nm): 1064
Dimensions (mm): 12.5 x 12.5 x 12.5 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%): >95
S-Polarization Reflection (%): >99.5
Substrate: N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View