

TECHSPEC® 12.5mm 70R/30T Cube Beamsplitter



Stock #68-536 ☐ In Stock

⊖ 1 ⊕ **€199,00**

ADD TO CART

Qty 1-5
€199,00

Qty 6+
€159,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Coating:
λ/4 MgF₂ @ 550nm on Faces
Multilayer Dielectric on Hypotenuse

Construction: Cube
Dimensions (mm): 12.5 x 12.5 x 12.5 ±0.10
Reflection/Transmission Ratio (R/T): 70/30
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View