

TECHSPEC® 12.5mm Dia., Nd:YAG Hard Coated OD 4.0 10nm Bandpass Filter Kit (4 Filters)



Stock #15-097 [CONTACT US](#)

- 1 + **€623,00**

ADD TO CART

Qty 1+
€623,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 12.50
Optical Density OD (Average): ≥4.0
Full Width-Half Max FWHM (nm): 10.00
Filters Included : Center Wavelengths: 266nm , 355nm , 532nm , 1064nm

Coating: Hard Coated
Type: Bandpass Filter
Typical Applications: Nd:YAG Laser Line Cleanup
Wavelength: Nd:YAG
Number of Filters: 4
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A, 3.4.1.1 Abrasion: MIL-C-48497A, 3.4.1.3 Temperature: MIL-C-48497A, 3.4.2.1 Cleaning: MIL-C-48497A, 3.4.2.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View