

12.5mm Diameter 120 Grit Ground Glass Diffuser



Stock **#83-418** ☐ In Stock

-

1

+

€12,25

ADD TO CART

Qty 1-10
€12,25
Qty 11+
€11,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit: ☐

Substrate: ☐
Float Glass

Thickness (mm):
1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
350 - 2000

Note:
Sandblasted on first surface

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
