

TECHSPEC® 125mm, Center Drive, Standard Top, English Extended Micrometer



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock **#66-452** 3-4 DAYS

⊖ 1 ⊕

€699,00

ADD TO CART

Qty 1-2

€699,00

Qty 3+

€611,80

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive: English Micrometer
Drive Orientation: Center Drive
Type: English
Stage Size (mm): 125 x 125
Travel (inches): 2
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 20
Mounting Threads: (21) 1/4-20, (8) 2-56, (4) 6-32
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 40
Yaw (arcsec): 30

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)