

## 12.5mm Diameter, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#27-402** 3-4 DAYS

⊖ 1 ⊕ **€15,00**

ADD TO CART

Qty 1-5

€15,00

Qty 6+

€12,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Diameter (mm):**  
12.50 ±0.76

**Surface Flatness (P-V):**  
4 - 6λ

**Substrate:** ☐  
Float Glass

|                                                                     |
|---------------------------------------------------------------------|
| <b>Surface Quality:</b><br>80-50                                    |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >85% @400 - 700nm |
| <b>Coating:</b><br>Protected Aluminum (400-700nm)                   |
| <b>Coating Type:</b><br>Metal                                       |
| <b>Angle of Incidence (°):</b><br>45.00                             |
| <b>Bevel:</b><br>Protective as needed                               |
| <b>Thickness (mm):</b><br>1.00 Nominal                              |
| <b>Thickness Tolerance (mm):</b><br>Nominal                         |
| <b>Type:</b><br>Flat Mirror                                         |
| <b>Wavelength Range (nm):</b><br>400 - 700                          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |

---