

12.5mm Diameter Unmounted, Linear Glass Polarizing Filter



Stock **#43-784** ☐ In Stock

-

1

+

€41,00

ADD TO CART

Qty 1-5
€41,00

Qty 6+
€32,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 12.50
Extinction Ratio: 100:1
Substrate: ☐ Polymer Film on B270

Operating Temperature (°C): -15 to +70
Surface Quality: 80-50
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): Single: ~30
Type: Linear Polarizer
Parallelism (arcmin): <3
Dimensional Tolerance (mm): +0.0/-0.2
Bevel: Protective bevel as needed
Construction: Dichroic Polarizing Film on Glass
Edges: Cut
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): 4 - 6λ
Polarization Efficiency (%): 95

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View
