

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 12.5mm FL T/4, Rugged Blue Series M12 Lens



12.5mm FL Rugged Blue Series M12 Lens



Stock #36-373 3-4 DAYS



1



€100,00

ADD TO CART

Qty 1+

€100,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
22.90

Horizontal Field of View, 1/2" Sensor:
78.0mm - 28.8°

Maximum Diameter (mm):
15

Outer Diameter (mm):

15
Weight (g): 6
Horizontal Field of View, 1/3" Sensor: 58.4mm - 21.8°
Maximum Image Circle (mm): 8.00
Numerical Aperture NA, Object Side: 0.0095
Horizontal Field of View @ Max Sensor Format: 78.0mm - 28.8°
Number of Elements (Groups): 5(5)
Wavelength Range (nm): 400 - 700
Horizontal Field of View, 1/2.5" Sensor: 70.6mm - 26.2°
Type: M12 Imaging Lens
Focal Length FL (mm): 12.50
Primary Magnification PMAG: 0.082X
Maximum Sensor Format: 1/2"
Working Distance (mm): 150 - ∞
Mount: M12 x 0.5 (S-Mbunt)
Aperture (f/#): f/4
Distortion (%): -0.36 @ Full Field
Back Focal Length BFL (mm): 10.1 - 9.7
Coating Specification: M4 MgF ₂ @ 550nm
Entrance Pupil Position (mm): 10.87
Horizontal Field of View, 1/4" Sensor: 43.8mm - 16.4°
Object Space Principal Plane (mm): 10.14
Image Space Principal Plane (mm): -3.01
Field of View at Max Sensor Format: Horizontal: 78.1mm - 28.9° Vertical: 58.5mm - 21.8° Diagonal: 97.7mm - 35.7°
IR Cut Filter: No
Exit Pupil Position (mm): -2.33
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View