

12.5mm FL SWIR Series Fixed Focal Length Lens



Stock #83-816 3-4 DAYS

- 1 + **€2.105,00**

ADD TO CART

Qty 1+
€2.105,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm): 300.00
Iris Option: Variable
Length (mm): 52.00
Filter Thread: M35.5 x 0.50
Maximum Diameter (mm): 42.0

Weight (g): 160
Horizontal Field of View, 1" Sensor: 55.6°
Maximum Image Circle (mm): 16.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 12.50
Maximum Sensor Format: 1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Distortion (%): <-2.0
Lens Wavelength Range: SWIR

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View