

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #49-418 3-4 DAYS



1



€167,50

ADD TO CART

Qty 1-5

€167,50

Qty 6+

€134,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Length (mm):
12.50

Coating:
Uncoated

Angle Tolerance (arcsec):
±5

Beam Deviation (arcsec): ±30
Dimensional Tolerance (mm): ±0.1
Image Orientation: Beam Deviation
Ray Deviation (°): 0.00
Substrate: N-BK7
Surface Quality: 40-20
Type: Rhomboid Prism
Wavelength Range (nm): 350 - 2200
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View