

TECHSPEC® 12.7 x 12.7mm Enhanced Aluminum, 4-6λ Mirror



Stock **#83-484** 3-4 DAYS

- 1 + **€24,00**

ADD TO CART

Qty 1-5
€24,00
Qty 6+
€18,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

12.7 x 12.7
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} ≥95% @ 450 - 650nm @ 45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 11.70 x 11.70
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 12.70
Width (mm): 12.70
Damage Threshold, By Design: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant