

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.7 mm Dia. 355nm, Nd:YAG Laser Line Beam Sampler



TECHSPEC® Nd:YAG Laser Line Beam Samplers

Stock #39-001 3-4 DAYS



1



€122,50

ADD TO CART

Qty 1-5

€122,50

Qty 6+

€110,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0 ±5

Clear Aperture (%):
90

Coating:
Laser V-Coat (355nm)

Coating Specification: R_{abs} <0.25% @ 355nm
Design Wavelength DWL (nm): 355
Diameter (mm): 12.70 +0.00/-0.10
Index of Refraction n_d: 1.458
Parallelism (arcmin): <3
Substrate: Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Beam Sampler
Damage Threshold, By Design: 7.5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View