

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC

12.7mm H x 12.7mm L x 12.5mm FL Vis-NIR, Illumination Grade PCX Cylinder Lens



Stock #36-217 3-4 DAYS



1



€82,00

ADD TO CART

Qty 1-5

€82,00

Qty 6+

€65,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
12.50

Substrate: ☐
[N-BK7](#)

f#:

0.984251968503937
Numerical Aperture NA: 0.51
Coating: VIS-NIR (400-1000nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 1000
Back Focal Length BFL (mm): 8.15
Center Thickness CT (mm): 6.60
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 1.33
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 6.46
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant