

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

12.7 mm Dia 1/2 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock #48-165 □ In Stock



1



€55,00

ADD TO CART

Qty 1-10

€55,00

Qty 11+

€45,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.70 ±0.1

Effective Focal Length EFL (mm):
25.40 @ 632.8nm

Numerical Aperture NA: 0.25
Back Focal Length BFL (mm): 23.20
Substrate:  PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: Uncoated
Clear Aperture CA (mm): 11.4
Edge Thickness ET (mm): 2.00
Center Thickness CT (mm): 3.34
f/#: 2.00
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 12.45
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View