

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock #39-524 3-4 DAYS

[Other Coating Options](#)



1



€186,00

ADD TO CART

Qty 1-10

€186,00

Qty 11+

€167,40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.10

Effective Focal Length EFL (mm):
25.40 @ 10.6µm

Back Focal Length BFL (mm): 24.36
Coating: Uncoated
Substrate:  Coherent® Infrared ZnSe
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Power (P-V) @ 10.6μm: λ 10
Irregularity (P-V) @ 10.6μm: λ 20
Centering, ETD (μm): ≤50.8
Center Thickness CT (mm): 2.50 ±0.10
Edge Thickness ET (mm): 1.93
Radius R₁ (mm): 35.63
Clear Aperture CA (mm): 11.43
f#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 18000
Bulk Absorption Coefficient (cm⁻¹): <0.0005 @ 10.6μm
Surface Roughness (Angstroms): <50 RMS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View