

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.7mm Dia. X 38.1mm FL, VIS-EXT Coated Plano-Convex Lens



Stock #88-690 3-4 DAYS

[Other Coating Options](#)



1



€43,00

ADD TO CART

Qty 1-9

€43,00

Qty 10+

€38,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                                       |
|---------------------------------------------------------------------------------------|
| 38.10 @ 587.6nm                                                                       |
| <b>Back Focal Length BFL (mm):</b><br>36.12                                           |
| <b>Coating:</b><br>VIS-EXT (350-700nm)                                                |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <0.5% @ 350 - 700nm                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                   |
| <b>Surface Quality:</b><br>40-20                                                      |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                 |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                           |
| <b>Focal Length Tolerance (%):</b><br>±1                                              |
| <b>Centering (arcmin):</b><br><1                                                      |
| <b>Center Thickness CT (mm):</b><br>3.00 ±0.10                                        |
| <b>Edge Thickness ET (mm):</b><br>1.95                                                |
| <b>Radius R<sub>1</sub> (mm):</b><br>19.69                                            |
| <b>Clear Aperture CA (mm):</b><br>11.7                                                |
| <b>f/#:</b><br>3                                                                      |
| <b>Numerical Aperture NA:</b><br>0.17                                                 |
| <b>Type:</b><br>Plano-Convex Lens                                                     |
| <b>Bevel:</b><br>Protective bevel as needed                                           |
| <b>Wavelength Range (nm):</b><br>350 - 700                                            |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |